

Product data sheet

Characteristics

415/110-WE

SOCKET FLUSH 3PIN 10A 110V



Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Flush
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	110 V AC
Depth	27 mm
Length	94 mm
Width	42 mm
Fixing center	84 mm




Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Package 1 Weight	0.080 kg
Package 1 Height	27.000 mm
Package 1 width	42.000 mm
Package 1 Length	94.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
