

Product data sheet

Characteristics

438S15-GY

SOCKET W-8MM SHROUD 15A250V



Main

Range of product	Standard Series
Colour	Grey
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	GY
Marking	Without marking
Local signalling	Without light indicator
Material	PVC (polyvinyl chloride)
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC
Depth	71 mm
Diameter	43 mm

Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Package 1 Weight	63.000 g
Package 1 Height	62.000 mm
Package 1 width	100.000 mm
Package 1 Length	90.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile