

Product data sheet

Characteristics

438S15HD-WE

socket cord extension with 8mm shroud 1.5sq
heavy duty flexible 15a, white



Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Connections - terminals	Screw terminals
Local signalling	Without light indicator
Material	PVC (polyvinyl chloride)
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Depth	79 mm
Diameter	49 mm
Number of poles	1
Poles description	1P + N + E
Cable outer diameter	12 mm
Pin number	3
Device composition	Flat pin
Targeted country	New Zealand Australia

Environment

Standards	AS/NZS 3120:2011/A1
Quality labels	RCM

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.6 kg
Package 1 Height	4.9 cm
Package 1 width	4.9 cm
Package 1 Length	7.9 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile