

Product data sheet

Characteristics

4PSO10DL

Socket outlet, MAX4, 10 A, 250 V, 3 pin, 2.5 module, double pole with earth



Main

Range of product	Series 4
Product brand	Clipsal



Complementary

Number of poles	2
Mounting support	DIN rail
[In] rated current	10 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Voltage colour	Blue
Duration	6 h
Socket number	1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	121 g
Package 1 Height	52 mm
Package 1 width	75 mm
Package 1 Length	90 mm
Unit Type of Package 2	CAR
Number of Units in Package 2	40
Package 2 Weight	40 kg
Package 2 Height	25 cm
Package 2 width	21.4 cm
Package 2 Length	33.8 cm

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration