

## Product data sheet

### Characteristics

# 4PSO15D

Socket outlet, MAX4, 15 A, 250 V, 3 pin, 2.5 module, double pole



### Main

Range of product	Series 4
Product brand	Clipsal




### Complementary

Number of poles	2
Mounting support	DIN rail
[In] rated current	15 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Voltage colour	Blue
Duration	6 h
Socket number	1

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	121 g
Package 1 Height	56 mm
Package 1 width	94 mm
Package 1 Length	81 mm

### Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.