

## Product data sheet

### Characteristics

# 4RCBE210/10

## Residual current breaker with overcurrent protection (RCBO), MAX4, 2P, 10 A, C curve, 10000 A, 240 V, 10 mA, A type



### Main

Range	MAX4
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Poles description	2P
Number of modules	2
[In] rated current	10 A
Curve code	C
Earth-leakage sensitivity	10 mA
Earth-leakage protection class	Type A
Breaking capacity	10000 A

### Complementary

[Ue] rated operational voltage	240 V AC
[Uimp] rated impulse withstand voltage	4 kV
Size	81 x 36 x 77.5 mm conforming to DIN 43880


### Environment

Standards	AS/NZS 61009
IP degree of protection	IP20 IP40
Ambient air temperature for operation	-5...40 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	207.0 g
Package 1 Height	4 cm
Package 1 width	8.5 cm
Package 1 Length	10 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>