

Product data sheet

Characteristics

4RCBE216/10

Clipsal MAX4, RCBO 2 module 2P 16A C curve 10 mA Type A 10000A



Main

Range	MAX4
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Poles description	2P
Number of modules	2
[In] rated current	16 A
Curve code	C
Earth-leakage sensitivity	10 mA
Earth-leakage protection class	Type A
Breaking capacity	10000 A

Complementary

[Ue] rated operational voltage	240 V AC
[Uimp] rated impulse withstand voltage	4 kV
Mounting support	DIN rail

Environment

Standards	AS/NZS 61009
IP degree of protection	IP20 IP40
Ambient air temperature for operation	-5...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.4 cm
Package 1 Width	10.0 cm
Package 1 Length	4.1 cm
Package 1 Weight	208.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Sustainable packaging	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations