

Product data sheet

Characteristics

4SSO15D15

Switched Socket outlet, Clipsal - Max 4, DIN Mounted 1 Gang 15 A 250 V 3 pin 4 module double pole

Main

Range of product	Series 4
Product brand	Clipsal
Device application	Power supply




Complementary

Number of poles	3
Number of modules	2
Number of power socket outlets	1 protective cover
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.6 cm
Package 1 Width	8.5 cm
Package 1 Length	7.3 cm
Package 1 Weight	103.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	40
Package 2 Height	25.0 cm
Package 2 Width	21.4 cm
Package 2 Length	33.8 cm
Package 2 Weight	4.12 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
SCIP Number	Ed9f2ac6-4e1a-4996-9399-2db36f9e19b7
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	China RoHS Declaration
Circularity Profile	No need of specific recycling operations
Take-back	No
