

## Product data sheet

### Characteristics

# 5031PEWP-GY

## C-Bus Control and Management System, Light Level Sensor, 40 - 1600lux, 180deg, Weatherproof



### Main

Range	C-Bus
Product brand	Clipsal
Colour	Grey

### Complementary

[Us] rated supply voltage	15...36 V DC
Network type	DC
Colour code	GY




### Environment

Ambient air temperature for operation	0...50 °C
---------------------------------------	-----------


### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	11.5 cm
Package 1 Length	11.8 cm
Package 1 Weight	333.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	11.7 cm
Package 2 Width	25.0 cm
Package 2 Length	31.0 cm
Package 2 Weight	2.72 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes

---

Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

---