


# Product data sheet

## Characteristics

# 5085EDLW-PW

Clipsal C-Bus, Wall Plate, Saturn, Enhanced Dynamic Labelling Technology, 5 Key Grid



### Main

Range	C-Bus
Product brand	Clipsal
Product name	C-Bus Saturn
Product or component type	Wall plate
Device application	Control

### Complementary

Colour	Cover plate: pure white Grid: white
Provided equipment	Mounting plate Flying lead
Control type	5 x push-button dual-action
Local signalling	Status: LED (tri-colour) on push-button
Switch application	Lighting Timer Audio Blind control Fan speed control Scene control On/Off switching Shutter control Dimming up/down control Page navigation
Local display	Backlit LCD display
Display type	Colour TFT display
Display size	2.8 inch
Messages display capacity	Up to 4 pages
Information displayed	Load type Temperature Power Date Time Operating mode
Number of outputs	16 in 4 page option 5 in 1 page option
Function of module	Proximity sensor monitoring wake-up
Communication port protocol	C-Bus - 2 wires
[Us] rated supply voltage	15...36 V: DC
Maximum supply current	32 mA
Material	Glass
Connector type	Mini USB port (rear) Socket (rear) for C-Bus
Function available	Firmware update by USB

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

User language	Multi-language
Product compatibility	LAN cable Cat. 5e
Electrical connection	Flying lead
Clamping connection capacity	0.2...1.5 mm <sup>2</sup>
Fixing mode	By screws
Mounting support	Wall
Width	77 mm
Height	123 mm
Depth	35 mm
Embedding depth	23.5 mm
Colour code	PW

## Environment

IP degree of protection	IP20
Ambient air temperature for operation	5...45 °C
Product certifications	CE[RETURN]RCM

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.8 cm
Package 1 Width	11.0 cm
Package 1 Length	16.0 cm
Package 1 Weight	198.0 g
Unit Type of Package 2	PAL
Number of Units in Package 2	240
Package 2 Height	103.0 cm
Package 2 Width	66.0 cm
Package 2 Length	67.5 cm
Package 2 Weight	97.082 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	8
Package 3 Height	20.6 cm
Package 3 Width	22.5 cm
Package 3 Length	33.0 cm
Package 3 Weight	2.903 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins