

Product data sheet

Characteristics

5086NL-680

Wall Plate, C-Bus, Saturn, key input unit, A-Series, 6 keys, saturn black



Main

Product brand	Clipsal
Range	C-Bus
Product name	C-Bus Saturn A Series
Product or component type	Switch
Device application	Control

Complementary

Device presentation	Basic element with full cover plate
Colour	Saturn black
Number of gangs	6 gangs
Control type	Push-button
Provided equipment	Fascia plate Body switch Push-button cap
Material	Plastic
[Ue] rated operational voltage	15...36 V DC
[In] rated current	22 mA
Communication network type	C-Bus 50
Input impedance	50 kOhm at 1 kHz
Isolation voltage	3.75 kV from C-Bus to mains
Switch function	Load switching Dimmer Time switch function Scene control Roller shutter Bell push switch Curtain
Local signalling	LED (blue/orange) for status
Time delay range	5 s
Connections - terminals	Terminal block - 0.2...1.3 mm ² (AWG 24...AWG 16)
Mounting support	Wall box
Fixing center	84 mm
Width	75 mm
Height	116 mm
Depth	28 mm
Net weight	54 g

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 % non-condensing

Packing Units

Package 1 Weight	0.220 kg
Package 1 Height	0.300 cm
Package 1 width	0.760 cm
Package 1 Length	1.150 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information