

Product data sheet

Characteristics

5101R

RELAY C-BUS 1 CHANNEL 10A



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Relay
Device application	Control

Complementary

[Us] rated supply voltage	15...36 V DC
Maximum switching current	10 A
Network type	AC/DC
Switching power	2300 W
Number of channels	1
Connector type	Screw terminals
Width	198 mm
Height	39 mm
Depth	42 mm

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Package 1 Weight	0.343 kg
Package 1 Height	35.000 mm
Package 1 width	50.000 mm
Package 1 Length	150.000 mm

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.