

Product data sheet

Characteristics

5504CMU

C-Bus Control and Management System, Current Measurement Unit, Accommodate Up to Four 2-Wire Current



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Current measurement device
Device application	Measure Monitoring Control

Complementary

[Ue] rated operational voltage	15...36 V DC
Maximum load current	80 A
Number of modules	4
Type of measurement	0...80 A current on load
Mounting support	DIN rail

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	11 cm
Package 1 Length	15.5 cm
Package 1 Weight	234 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	26 cm
Package 2 Width	22 cm
Package 2 Length	34 cm
Package 2 Weight	2.15 kg
Unit Type of Package 3	P12
Number of Units in Package 3	240
Package 3 Height	80 cm
Package 3 Width	120 cm
Package 3 Length	100 cm
Package 3 Weight	73.5 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes