

Product data sheet

Characteristics

5754ODPE

OCCUPANCY, LIGHT LEVEL SENSOR

SURFACE MOUNT 360 DEGREE



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Occupancy and light level sensor
Device application	Lighting
Product specific application	Staircase monitoring
Sensor type	PIR
Colour	White

Complementary

Protection type	Creep zone protection
Type of setting	Light sensitivity adjustable
Number of channels	1
Time delay range	0...1 s (switch-on)
Detection face	Lateral: 4.85 m Frontal: 4.85 m
Movement detection area	9.7 m
Horizontal detection angle	0...360 °
Duty cycle	1080 min
Material	Plastic
Device mounting	Surface
Mounting height	2.7 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	116 g
Package 1 Height	40 mm
Package 1 width	101 mm
Package 1 Length	101 mm
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Weight	2.747 kg
Package 2 Height	16 cm
Package 2 width	28 cm
Package 2 Length	33.5 cm
Unit Type of Package 3	P12
Number of Units in Package 3	960
Package 3 Weight	140.856 kg
Package 3 Height	80 cm
Package 3 width	120 cm
Package 3 Length	110 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins