

Product data sheet

Characteristics

60PB

Switch 60 Series Mechanism - Push-button - 1- or 2-way - 250 V - 20 A / 16 AX



Main

Range of product	Saturn Series 4000
Product or component type	Push-button
Product brand	Clipsal
Device presentation	Basic element


Complementary

Actuator	Push-button
Local signalling	Without light indicator
Fixing mode	By screws
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
Inrush current	20 A
Height	23.5 mm
Depth	40 mm
Embedding depth	31.6 mm
Width	23.5 mm
Mounting position	Vertical

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	22.0 g
Package 1 Height	3 cm
Package 1 width	3 cm
Package 1 Length	5.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile