

## Product data sheet

### Characteristics

# 60PBI

## Saturn Series, Push Button Mechanism, Intermediate, 230/240V, 10AX



### Main

Range of product	Saturn Series
Product or component type	Push-button
Product brand	Clipsal
Device presentation	Basic element

### Complementary

Actuator	Push-button
Local signalling	Without light indicator
[Ue] rated operational voltage	250 V AC
Inrush current	10 A
Height	23.5 mm
Depth	40 mm
Embedding depth	31.6 mm
Width	23.5 mm
Load type	LEDi lamp 100 W Fluorescent lamp 10 AX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	4.6 cm
Package 1 Length	3.1 cm
Package 1 Weight	26.0 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>