

Product data sheet

Characteristics

60PBL

Clipsal Saturn 4000, Switch Mechanisms Push-Button, 250V, 16AX/20A, 1 Way, 2 Way, LED



Main

Range of product	Saturn Series 4000
Product or component type	Push-button
Product brand	Clipsal
Device presentation	Basic element
Colour tint	Black

Complementary

Actuator	Push-button
Local signalling	Indicator light
Fixing mode	By screws
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	230/240 V AC
Inrush current	20 A
Height	23.5 mm
Depth	40 mm
Embedding depth	31.6 mm
Width	23.5 mm
Mounting position	Vertical
Load type	Fluorescent 20 A LEDi lamp 250 W

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	3.2 cm
Package 1 Length	6.6 cm
Package 1 Weight	24 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
