

# Product data sheet

## Characteristics

# 60RSM3

## Switch Mechanisms, Saturn Series, 4 Position Rotary, 3 On 1 Off



### Main

Range of product	Saturn Series 4000
Product brand	Clipsal
Assembly Type	Basic element

### Complementary

Control type	Rotary knob
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	4 cm
Package 1 Length	11.3 cm
Package 1 Weight	24 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations