

Product data sheet

Characteristics

645/2-BK

Clipsal - Cable Management, Mains
Connection Box, Unfused, 2 Terminal, 20mm
Screwed Entry



Main

Colour	Black
Product brand	Clipsal
Provided equipment	Cover
Cover type	Transparent

Complementary

Colour code	BK
Number of clamp	2
Fixing mode	By screws
Cable entry number	1
Material	PA (polyamide) 6

Environment

IP degree of protection	IP30
Dust zone	-

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	6.6 cm
Package 1 Length	6.8 cm
Package 1 Weight	118 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	77 cm
Package 2 Width	138 cm
Package 2 Length	239 cm
Package 2 Weight	1.28 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	245 cm
Package 3 Width	253 cm
Package 3 Length	298 cm
Package 3 Weight	6.4 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations