

# Product data sheet

## Characteristics

# 7005A

## FAN EXH WIND 150MM-AUTO LOUVRE



### Main

|               |         |
|---------------|---------|
| Product brand | Clipsal |
|---------------|---------|

### Complementary

|                                |                  |
|--------------------------------|------------------|
| [Ue] rated operational voltage | 230...240 V AC   |
| Air flow                       | 360 m3/h         |
| Diameter                       | 148 mm impeller: |
| Power consumption in W         | 45 W             |
| [In] rated current             | 0.27 A full load |

### Environment

|                         |      |
|-------------------------|------|
| IP degree of protection | IPx4 |
|-------------------------|------|

### Packing Units

|                  |            |
|------------------|------------|
| Package 1 Weight | 2306.000 g |
| Package 1 Height | 203.000 mm |
| Package 1 width  | 245.000 mm |
| Package 1 Length | 250.000 mm |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |