

# Product data sheet

## Characteristics

# 7008A

## Airflow, Performance Exhaust Fan, Wall Mount, 150mm, Pull Cord



### Main

Product brand	Clipsal
---------------	---------

### Complementary

[Ue] rated operational voltage	230...240 V AC
Air flow	360 m3/h
Diameter	148 mm impeller:
Power consumption in W	45 W
[In] rated current	0.27 A full load

### Environment

IP degree of protection	IPx4
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.8 cm
Package 1 Width	25.0 cm
Package 1 Length	25.2 cm
Package 1 Weight	2.02 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations <a href="#">Circularity Profile</a>