

Product data sheet

Characteristics

7008A

Airflow, Performance Exhaust Fan, Wall Mount, 150mm, Pull Cord



Main

Range of product	Airflow MaxAir
Product brand	Clipsal

Complementary

[Ue] rated operational voltage	230...240 V AC
Air flow	360 m3/h
Diameter	148 mm impeller:
Power consumption in W	45 W
[In] rated current	0.27 A full load

Environment

IP degree of protection	IPx4
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.8 cm
Package 1 Width	25.0 cm
Package 1 Length	25.2 cm
Package 1 Weight	2.02 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations Circularity Profile