

Product data sheet

Characteristics

750WP-GY

Motion Sensor Infrascan - Passive infrared -
Outdoor - 18m detection range - 2-Wire - 240 V
- 5 A - Grey



Main

Range	Infrascan
Product brand	Clipsal
Product or component type	Movement sensor
Colour	Grey

Complementary

[Ue] rated operational voltage	200...265 V AC
Network frequency	50 Hz
Power range	<= 40 W
Mounting support	Wall Ceiling
Mounting height	2.4 m
Colour code	GY

Environment

IP degree of protection	IP66
Ambient air temperature for operation	0...50 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.38 kg
Package 1 Height	85 mm
Package 1 width	130 mm
Package 1 Length	165 mm

Offer Sustainability

EU RoHS Directive	Under investigation
China RoHS Regulation	China RoHS Declaration
Circularity Profile	End Of Life Information

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.