

Product data sheet

Characteristics

750WPR-GY

Motion Sensor Infrascan - Passive infrared - Outdoor - 18m detection range - 3-wire - 240 V - 10 A - Grey



Main

Range	Infrascan
Product brand	Clipsal
Product or component type	Movement sensor
Colour	Grey

Complementary

[Ue] rated operational voltage	200...265 V AC
Network frequency	50 Hz
Mounting support	Wall Ceiling
Mounting height	2.4 m
Colour code	GY

Environment

IP degree of protection	IP66
Ambient air temperature for operation	0...50 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	331 g
Package 1 Height	16.5 cm
Package 1 width	12.6 cm
Package 1 Length	8.3 cm

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Circularity Profile	End Of Life Information