

Product data sheet

Characteristics

9016TCM-GY

conduit corrugated turbo pvc medium duty

16mm / 50m



Main

| | |
|---------------|---------|
| Colour | Grey |
| Product brand | Clipsal |

Complementary

| | |
|-------------------|--------------------------|
| Colour code | GY |
| Material | PVC (polyvinyl chloride) |
| Stub stiffness | Flexible |
| Diameter | Internal: 10.3 mm |
| External diameter | 16 mm |

Environment

| | |
|---------------------------------------|----------------------------|
| Environmental characteristic | Conforming to AS/NZS 61386 |
| Ambient air temperature for operation | -15...60 °C |

Packing Units

| | |
|------------------|------------|
| Package 1 Weight | 8.120 kg |
| Package 1 Height | 198.000 mm |
| Package 1 width | 280.000 mm |
| Package 1 Length | 292.000 mm |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |