

Product data sheet

Characteristics

9025TCM10-GY

Corrugated Conduit, Clipsal - Cable Management, Medium Duty, PVC, 25mmx10m



Main

Colour	Grey
Product brand	Clipsal

Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Stub stiffness	Flexible
Diameter	Internal: 18 mm
External diameter	25 mm

Environment

Environmental characteristic	Conforming to AS/NZS 61386
Ambient air temperature for operation	-15...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	37.8 cm
Package 1 Length	37.8 cm
Package 1 Weight	1.24 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

