

Product data sheet

Characteristics

9032CMS-GY

Corrugated Conduit, Clipsal - Cable Management, Medium Duty Sheathed, PVC, 32mmx25m

Main

Colour	Grey
Product brand	Clipsal

Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Stub stiffness	Flexible
Diameter	Inner: 24.3 mm
External diameter	32 mm

Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	39.8 cm
Package 1 Length	31.6 cm
Package 1 Weight	6.2 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	40
