

Product data sheet

Characteristics

ACTFMFXC

Actassi FLEX Fiber Front Cover (4pcs)



Main

Range of product	Actassi
Product name	Actassi FLEX
Product or component type	Fibre front cover
Quantity per set	4

Complementary

Range compatibility	Actassi Actassi FLEX fibre cassette Actassi Actassi FLEX fibre patch panel
Product compatibility	LC duplex adaptor
Number of rack unit	1U
Integrated connection type	Duplex LC, multi mode transmission mode
Number of port per front cover	12
Height	44.45 mm
Length	109.5 mm
Width	9.45 mm


Environment

Ambient air temperature for operation	0...55 °C
Ambient air temperature for storage	-20...65 °C
Product certifications	UL

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	11.6 cm
Package 1 Length	16.1 cm
Package 1 Weight	175 g

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile