

Product data sheet

Characteristics

ACTFMFXU

Actassi FLEX Empty Fiber Panel



Main

Range of product	Actassi
Product name	Actassi FLEX
Product or component type	Fibre patch panel
Provided equipment	Fibre cassette not included

Complementary

Range compatibility	Actassi Actassi FLEX fibre cassette Actassi Actassi iFLEX upgrade kit Actassi Actassi iFLEX fibre front cover
Communication port support	Fiber optic
Number of rack unit	1U
Material	Plastic RAL 7016 Steel RAL 9005
Mounting support	19" rack
Height	44.45 mm
Length	482.6 mm
Width	114.5 mm
Targeted region	Asia Pacific.





Environment

Ambient air temperature for operation	0...55 °C
Ambient air temperature for storage	-20...65 °C
Product certifications	UL

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.1 cm
Package 1 Width	17 cm
Package 1 Length	51 cm
Package 1 Weight	706 g

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile