

Product data sheet

Characteristics

ACTFMSPTKIT

Actassi, 1U Fusion splice tray kit (max. 24-fiber)



Main

Range of product	Actassi
Product or component type	Optic splice cassette
Colour	Cassette: grey

Complementary

Range compatibility	Actassi 19" fibre optic panel
Product destination	Empty fibre optic panel
Device composition	1 cover 1 splice tray 2 insert 2 cable disc 1 cable gland 1 cable gland holder 4 screw 4 nut 30 heat shrink splice protector tube 4 ring
Number of port	24
Material	ABS (acrylonitrile butadiene-styrene)
Mounting type	By 2 screws with fibre patch panel By rivet with fibre patch panel with quick-fix function
Length	155.2 mm
Height	10 mm
Width	92.4 mm
Targeted region	Asia Pacific. Europe

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	18.8 cm
Package 1 Length	19.2 cm
Package 1 Weight	258.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	36
Package 2 Height	30.0 cm
Package 2 Width	39.7 cm
Package 2 Length	59.8 cm

Package 2 Weight	9.988 kg
Unit Type of Package 3	P12
Number of Units in Package 3	432
Package 3 Height	102.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	132.356 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations