

## Product data sheet

### Characteristics

# ACTMPBP

## Actassi, Actassi Fibre Optic Front Adapters Plate Blank



### Main

|                     |                |
|---------------------|----------------|
| Range               | Actassi        |
| Product             | Blank plate    |
| Product destination | Optic cassette |

### Complementary

|             |         |
|-------------|---------|
| Fixing mode | Snap-in |
|-------------|---------|

### Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 4.7 cm    |
| Package 1 Width              | 4.7 cm    |
| Package 1 Length             | 14 cm     |
| Package 1 Weight             | 30.4 g    |
| Unit Type of Package 2       | CAR       |
| Number of Units in Package 2 | 96        |
| Package 2 Height             | 30 cm     |
| Package 2 Width              | 29.9 cm   |
| Package 2 Length             | 39.8 cm   |
| Package 2 Weight             | 3.618 kg  |
| Unit Type of Package 3       | P12       |
| Number of Units in Package 3 | 2304      |
| Package 3 Height             | 102 cm    |
| Package 3 Width              | 80 cm     |
| Package 3 Length             | 120 cm    |
| Package 3 Weight             | 89.165 kg |

### Offer Sustainability

|                        |                                                                                                                                                                                      |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| REACH Regulation       |  <a href="#">REACH Declaration</a>                                                                |
| REACH free of SVHC     | Yes                                                                                                                                                                                  |
| EU RoHS Directive      | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free | Yes                                                                                                                                                                                  |
| Mercury free           | Yes                                                                                                                                                                                  |
| China RoHS Regulation  |  <a href="#">China RoHS Declaration</a>                                                           |

|                            |                                                                                      |
|----------------------------|--------------------------------------------------------------------------------------|
| RoHS exemption information |  Yes |
| Circularity Profile        | No need of specific recycling operations                                             |