

# ACTPPAS24NS

Actassi angled patch panel, 24 ports, category 6, FTP, non shuttered, unloaded



### Main

Range of product	Actassi
Product or component type	Patch panel
Device presentation	Empty
Provided equipment	Without RJ45 connectors






### Complementary

[In] rated current	1.5 A
Number of port	24 port of FTP
Product compatibility	Standard 19" cabinet/rack
Communication network category	6 5e
Contact resistance	1 mOhm
Insulation resistance	>= 200 MOhm
Minimum number of matings	1000 cycles
Number of rack unit	1U
Type of connector	S-110 keystone

### Environment

Ambient air temperature for operation	-40...70 °C
Ambient air temperature for storage	-20...60 °C
Relative humidity	0...93 %
Standards	ANSI/TIA/EIA-568-B ISO/IEC 11801 Ed.2, 2002

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins