

Product data sheet

Characteristics

ACTPPFX6U24NSS

Actassi FLEX Cat 6 UTP 24-Port Patch Panel



Main

Range of product	Actassi
Product name	Actassi FLEX
Product or component type	Patch panel
Provided equipment	Adaptor plate Connector 24 6 UTP

Complementary

Number of port	24 port of UTP
Range compatibility	Actassi iFLEX copper front cover Actassi iFLEX upgrade kit
Mounting support	19" rack
Number of rack unit	1U
Product destination	Data center
Type of connector	S-110 keystone
Type of installation	Indoor
Length	482.6 mm
Width	114.5 mm
Height	44.45 mm

Environment

Ambient air temperature for operation	0...55 °C
Ambient air temperature for storage	-20...65 °C
Standards	ISO/IEC 11801 Ed.2, 2002 TIA/EIA-568-C.2 AS/NZS 3080:2003
Product certifications	UL

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile