



### Main

Range of product	Actassi
Product name	Actassi FLEX
Product or component type	Copper patch panel
Device presentation	Empty
Provided equipment	Adaptor plate not included Connector not included

### Complementary

Connector type	RJ45 UTP
Mounting type	On panel horizontal position
Function available	Real time patching detection after firmware upgrade
Number of port	24 port
Product compatibility	S-110 keystone UTP adaptor plate
Range compatibility	Actassi Actassi FLEX adaptor plate Actassi Actassi iFLEX upgrade kit Actassi Actassi iFLEX copper front cover
Communication port support	Copper cable
Mounting support	19" rack
Number of rack unit	1U
Product destination	Data center
Type of connector	S-110 keystone
Type of installation	Indoor
Material	Plastic RAL 7016 Steel RAL 9005
Length	482.6 mm
Width	114.5 mm
Height	44.45 mm

### Environment

Ambient air temperature for operation	0...55 °C
Ambient air temperature for storage	-20...65 °C
Product certifications	UL

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.1 cm
Package 1 Width	17 cm
Package 1 Length	51 cm
Package 1 Weight	692 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>