

## Product data sheet

### Characteristics

# B31A-BK

## Metal Plate Series, Flush Switch, 1 Gang, 250VAC, 10A, B Style, Architrave



### Main

Range of product	Metal Plate
Product brand	Clipsal
Assembly Type	Basic element with full cover plate and grid

### Complementary

Installation Type	Flush
Number Of Switches	1
Surface treatment	Stainless steel
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Mounting Type	By screws
Actuator	Rocker
Switch function	1-way 2-way

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	4.5 cm
Package 1 Length	11.0 cm
Package 1 Weight	68.0 g

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.