

## Product data sheet

### Characteristics

# B5032NL-BK

## C-Bus Control and Management System, Flat Plate, Key Input, 2 Gang, B Style, Learn Enabled, Stainless Steel



### Main

|                  |  |
|------------------|--|
| Range of product | Metal Plate Multi-Gang Series<br>C-Bus |
| Product brand    | Clipsal                                |


### Complementary

|                     |                 |
|---------------------|-----------------|
| Number of gangs     | 2 gangs         |
| Product destination | Switch          |
| Fixing mode         | By screws       |
| Control type        | Button          |
| Marking             | Without marking |
| Surface treatment   | Stainless steel |
| Mounting position   | Vertical        |
| Fixing center       | 84 mm           |
| Thickness           | 19 mm           |
| Length              | 116 mm          |
| Width               | 76 mm           |
| Colour code         | BK              |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 4.5 cm  |
| Package 1 Width              | 8.5 cm  |
| Package 1 Length             | 13.0 cm |
| Package 1 Weight             | 160.0 g |

### Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| RECh Regulation            |  <a href="#">RECh Declaration</a>       |
| EU RoHS Directive          | Compliant with Exemptions  |
| Mercury free               | Yes  |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a> |
| RoHS exemption information |  Yes                                    |

---

Environmental Disclosure

 [Product Environmental Profile](#)

---

Circularity Profile

 [End Of Life Information](#)

---