

# Product data sheet

## Characteristics

# BB15VA-BK

## Metal Plate Series, Socket Swt Sing B Style Bs



### Main

|                           |                 |
|---------------------------|-----------------|
| Range of product          | Metal Plate     |
| Product or component type | Switched socket |
| Product brand             | Clipsal         |

### Complementary

|                                |                         |
|--------------------------------|-------------------------|
| Control type                   | ON/OFF button           |
| Number of gangs                | 1 gang                  |
| Pin number                     | 3                       |
| Number of power socket outlets | 1                       |
| Actuator                       | Rocker Switch           |
| Fixing mode                    | By screws               |
| Local signalling               | Without light indicator |
| Mounting position              | Vertical                |
| Material                       | Brass                   |
| [Ue] rated operational voltage | 250 V AC                |
| [In] rated current             | 10 A                    |
| Depth                          | 35 mm                   |
| Length                         | 115 mm                  |
| Width                          | 70 mm                   |
| Fixing center                  | 84 mm                   |






### Environment

|           |   |
|-----------|---|
| Standards | AS/NZS 3100<br>AS/NZS 3112<br>AS/NZS 3133:approval number S/1 |
|-----------|---|

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 3.5 cm  |
| Package 1 Width              | 7 cm    |
| Package 1 Length             | 11.5 cm |
| Package 1 Weight             | 0.2 kg  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#"> REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#"> EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#"> China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#"> Yes</a>                           |
| Circularity Profile        | <a href="#"> End Of Life Information</a>       |