

Product data sheet

Characteristics

BB32A-WE

Metal Plate Series Switch 2Gang Architrave B Style Brass,White

Main

Range of product	Metal Plate
Range	Metal Plate
Product brand	Clipsal
Product or component type	Switch
Assembly Type	Basic element with full cover plate and grid
Device application	Control
Colour	White electric (RAL 9010)

Complementary

Number of gangs	2 gangs
Installation Type	Flush
Number Of Switches	2
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Mounting Type	By screws
Switch function	2-way 1-way

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.