

## Product data sheet

### Characteristics

# BBSL15XA-WE

## Metal Plate Series, Single Switch Socket Outlet 250V, 10A, BBSL Style, Flat Plate, Rm vb Extra Switch

### Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal

### Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number Of Outlets	1
Actuator	Switch Rocker
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Brass
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	130 mm
Width	86 mm
Mounting Centers	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	8.6 cm
Package 1 Length	13 cm
Package 1 Weight	180 g

## Offer Sustainability

---

REACH Regulation

 [REACH Declaration](#)

---

EU RoHS Directive

Compliant with Exemptions

---

China RoHS Regulation

 [China RoHS Declaration](#)

---