

## Product data sheet

### Characteristics

# BBSL25A-WE

## Metal Plate Series, Twin Switch Socket Outlet, 250V, 10A, BBSL Style, Flat Plate



### Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal

### Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Actuator	Switch Rocker
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Brass
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	35 mm
Length	130 mm
Width	86 mm
Mounting Centers	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	4 cm
Package 1 Length	13.2 cm
Package 1 Weight	144 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations