

Product data sheet

Characteristics

BBSL25XA-BK

Twin Switch Socket Outlet, Metal Plate Series, 250V, 10A, BBSL Style, Flat Plate, Rm vb Extra Switch



Main

Range of product	Metal Plate
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Actuator	Rocker Switch
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Brass
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	35 mm
Length	130 mm
Width	85 mm
Mounting Centers	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8.5 cm
Package 1 Length	13 cm
Package 1 Weight	180 g

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations