

Product data sheet

Characteristics

BSL32VA-WE

Flush Switch, Metal Plate Series, 2 Gang, 250VAC, 10A, Range, BSL Style, Standard, Vert

Main

Range of product	Metal Plate
Product brand	Clipsal
Assembly Type	Basic element with full cover plate and grid




Complementary

Installation Type	Flush
Number Of Switches	2
Surface treatment	Stainless steel
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Mounting Type	By screws
Actuator	Rocker
Switch function	2-way 1-way

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.4 cm
Package 1 Width	8.8 cm
Package 1 Length	13 cm
Package 1 Weight	180 g

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Take-back	No