

Product data sheet

Characteristics

C2015D4N-WE

Quad Switch Socket Outlet, Classic C2000 Series, Classic, 250V, 10A, 2 Pole, Neon

Main

Range of product	Classic Series C2000
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	4 gangs
Pin number	3
Number Of Outlets	4
Actuator	Switch Rocker
Mounting Type	By screws
Local signalling	Indicator light
Installation Orientation	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	116 mm
Width	76 mm
Mounting Centers	84 mm

Environment

Standards	AS/NZS 3112
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	7.7 cm
Package 1 Length	19.7 cm
Package 1 Weight	257 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	5 kg
Unit Type of Package 3	CAR

Number of Units in Package 3	50
Package 3 Height	225 mm
Package 3 Width	348 mm
Package 3 Length	445 mm
Package 3 Weight	50 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations