

Product data sheet

Characteristics

C2030-WE

Flush Switch, Classic C2000 Series, Architrave Size, 1 Gang, 250V, 10A



Main

Range of product	Classic Series C2000
Product brand	Clipsal
Assembly Type	Basic element with full cover plate

Complementary

Number of poles	1
Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Mounting Type	By screws
Surface finish	Glossy
Actuator	Rocker
Switch function	1-pole

Environment

Standards	AS/NZS 60669.1
-----------	----------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.3 cm
Package 1 Width	8.3 cm
Package 1 Length	5.2 cm
Package 1 Weight	34 g
Unit Type of Package 2	CAR
Number of Units in Package 2	300
Package 2 Height	254 cm
Package 2 Width	348 cm
Package 2 Length	445 cm
Package 2 Weight	11.4 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes