

Product data sheet

Characteristics

C2032VA-WE

Classic C2000 Series, Flush Switch 2 Gang, 250VAC, 10A, Classic , Standard, Vertical



Main

Range of product	Classic Series C2000
Product brand	Clipsal
Assembly Type	Basic element with full cover plate and grid

Complementary

Number of poles	1
Installation Type	Flush
Number Of Switches	2
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A 8 AX, fluorescent lamp
Marking	Without marking
Mounting Type	By screws
Surface finish	Glossy
Actuator	Rocker
Switch function	1-pole

Environment

Standards	AS/NZS 60669.1
-----------	----------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	7.6 cm
Package 1 Length	11.7 cm
Package 1 Weight	76 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations