

# Product data sheet

## Characteristics

# CEF40WK-WE

## Ducted Exhaust Fan Kit, Airflow, Airflow, Ceiling Mounted, 150mm



### Main

Range of product	Airflow
Product brand	Clipsal

### Complementary

[Ue] rated operational voltage	240 V
Air flow	290 m3/h
Power consumption in W	35 W
[In] rated current	0.15 A full load

### Environment

IP degree of protection	IPx4
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	31 cm
Package 1 Width	37 cm
Package 1 Length	37 cm
Package 1 Weight	4 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations <a href="#">Circularity Profile</a>