

Product data sheet

Characteristics

CLIFLS20LED

Clipsal - LED floodlight - 20W - IP65 - 4000K

Main

Range	Clipsal
Product name	FLS Series
Product or component type	Floodlight
Device application	Lighting

Complementary

Type of installation	Outdoor
Device mounting	Wall mounted
Device composition	Gasket Locking screws Microwave sensor Adjustable trunion arm
Total system power	20 W
Light source	LED 30 W
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	1400 lm
Colour rendering index	R _a =80
Bulb lifespan	36000 h
Colour temperature	4000 K
Beam angle	105 °
Height	Body: 134 mm Body with trunion arm: 180 mm
Width	213 mm
Depth	27.5 mm
Cable length	0.6 m

Environment

IP degree of protection	IP65
Ambient air temperature for operation	-10...45 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	20 cm
Package 1 Length	25 cm
Package 1 Weight	1.1 kg

EU RoHS Directive	Not compliant
-------------------	---------------