

Main

| | |
|---------------------------|------------|
| Range | Clipsal |
| Product name | FLS Series |
| Product or component type | Floodlight |
| Device application | Lighting |

Complementary

| | |
|--------------------------------|--|
| Type of installation | Outdoor |
| Device mounting | Wall mounted |
| Device composition | Gasket Locking screws Microwave sensor Adjustable trunion arm |
| Total system power | 20 W |
| Light source | LED 30 W |
| [Ue] rated operational voltage | 240 V AC 50 Hz |
| Luminous flux | 1400 lm |
| Colour rendering index | R _a =80 |
| Bulb lifespan | 36000 h |
| Colour temperature | 4000 K |
| Beam angle | 105 ° |
| Height | Body: 134 mm Body with trunion arm: 180 mm |
| Width | 213 mm |
| Depth | 27.5 mm |
| Cable length | 0.6 m |

Environment

| | |
|---------------------------------------|--------------------------|
| IP degree of protection | IP65 |
| Ambient air temperature for operation | -10...45 °C |
| Relative humidity | 10...95 % non-condensing |

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 8 cm |
| Package 1 Width | 20 cm |
| Package 1 Length | 25 cm |
| Package 1 Weight | 1.1 kg |

Offer Sustainability

EU RoHS Directive

Not compliant