

## Product data sheet

### Characteristics

# CLITPFLT100

LED floodlight, Clipsal - Lighting, 100W, 4000K, IP65, black



### Main

Range	Clipsal
Product or component type	Floodlight
Device application	Lighting
Main colour tint	Black
Colour tint	Black

### Complementary

Type of installation	Outdoor
Device mounting	Surface Ceiling
Total system power	100 W
Light source	LED
[Ue] rated operational voltage	230 V AC 50 Hz
Luminous flux	0...95 % RH non-condensing: 10500 lm
Colour rendering index	R <sub>a</sub> =80
Bulb lifespan	50000 h
Colour temperature	4000 K
Beam angle	110 °
Height	Outdoor: 357 mm
Width	260 mm
Depth	45 mm
Net weight	2.45 kg
Cable length	0.6 m

### Environment

Environmental characteristic	Weatherproof
IP degree of protection	IP65
Ambient air temperature for operation	-20...40 °C
Relative humidity	10...95 %

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	27.6 cm
Package 1 Length	32 cm
Package 1 Weight	2.087 kg

Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Height	31.5 cm
Package 2 Width	27.5 cm
Package 2 Length	35 cm
Package 2 Weight	11.136 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

### Contractual warranty

Warranty	3-Years
----------	---------