

## Product data sheet

### Characteristics

# CLITPFLT30PSC

LED Floodlight, Clipsal - Lighting, 30W, 20W, 15W, CCT, IP65, black

### Main

Range	Clipsal
Product or component type	Floodlight
Device application	Lighting
Main colour tint	Black
Colour tint	Black

### Complementary

Type of installation	Outdoor
Device mounting	Surface Ceiling
Total system power	30 W 20 W 15 W
Light source	LED
[Ue] rated operational voltage	230 V AC 50 Hz
Luminous flux	0...95 % RH non-condensing: 3150 lm 0...95 % RH non-condensing: 2100 lm 0...95 % RH non-condensing: 1575 lm
Colour rendering index	R <sub>a</sub> =80
Bulb lifespan	50000 h
Colour temperature	3000 K 4000 K 6000 K
Beam angle	110 °
Height	Outdoor: 116 mm
Width	86 mm
Depth	27 mm
Net weight	0.40 kg
Cable length	0.6 m

### Environment

Environmental characteristic	Weatherproof
IP degree of protection	IP65
Ambient air temperature for operation	-20...40 °C
Relative humidity	10...95 %

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.1 cm
Package 1 Width	17.5 cm
Package 1 Length	17.4 cm
Package 1 Weight	676 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	38 cm
Package 2 Width	20.5 cm
Package 2 Length	33 cm
Package 2 Weight	8.636 kg

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	205

## Contractual warranty

Warranty	3-Years
----------	---------